



Easy Guide to Choosing Your ODL Add-On Blind

1. Determine the type of glass frame on your door and follow the directions below each type of frame.

RAISED FRAME

Raised frame is raised from the door when running hand over frame and door glass




FLUSH FRAME


Flush frame is flush when running hand over door and frame - frame will appear inset into door



2. Measure the **outside** width & height of the door glass frame as shown below.



Measure the **inside** width & height of the door glass opening as shown below.



3. Choose the Add-On Blind product that fits your frame dimensions from the chart below.

Choose the Add-On Blind product that fits your door glass dimensions from the chart below.

RAISED FRAME Add-On Blind Sizes

	Ⓐ	Ⓑ
Product Description	Fits Width	Fits Height
Half View Narrow	21-3/4 in. – 22 in.	37-3/4 in. – 38 in.
*Half View Standard	23-3/4 in. – 24 in.	37-3/4 in. – 38 in.
*Full View Narrow	21-3/4 in. – 22 in.	65-3/4 in. – 66 in.
*Full View Standard	23-3/4 in. – 24 in.	65-3/4 in. – 66 in.
Half View Sidelite	9-3/4 in. – 10 in.	37-3/4 in. – 38 in.
*Full View Sidelite	8-3/4 in. – 9 in.	65-3/4 in. – 66 in.

*Colors in chart coordinate with color of band on packaging for easy selection.

FLUSH FRAME Add-On Blind Sizes

	Ⓐ	Ⓑ
Product Description	Fits Width	Fits Height
Full View Narrow	22 in. – 25-1/2 in.	63 in. – 66 in.
Full View Standard	25-1/2 in. – 28 in.	63 in. – 66 in.