



Step 15. Attach Stacking/Tilting Tub

Set the Rear Pegs of the Tilting Tub into the Rear Peg Slots in the Rear Frame. Lower the Tub to insert the Front Tub Pegs into the Front Frame Peg Holes. Apply light pressure to all four corners of the Tub to fully seat the pegs. NOTE: This Tub will tilt like a dump truck and can be easily lifted off the frame.

Step 16. Install Cargo Walls

The Flatbed has a square hole in each corner. Slide the short legs of the Cargo Walls into the two square holes of the flatbed on both ends. Add the Optional Tool Rack on any one of the three sets of elongated holes on either Cargo Wall to hold fishing poles or other tools. (Use the Tool Rack on rear Cargo Wall to line up with circular depressions on the Rear Frame.)



Lightweight



Portable



Expandable









Scan QR Code for detailed video assembly instructions

Copyright Mighty Max Cart LLC 2018

US Design Patent # D527,508 US Utility Patent # 7,441,783 B2. The first all terrain and all weather cart.

Congratulations! Now enjoy your Plus One Cart for many, many years to come.

See what other customers are using their carts for and share your ideas as well. Join our mailing list at:

www.mightymaxcart.com







Step 17. Optional Fishing Pole Holders

Set the Plus One Cart to its shortest You can purchase our heavy duty Fishing length. Set the Tub on the tapered tops of Pole Holders in sets of 2. Slide the two Fishing Pole Holders over the top posts of the Cargo Walls and press down on the the Front Cargo Wall and/or Rear Cargo corners to securely seat the tub. Now you have a double-decked carrier. Wall and snug fit them to the tapered tops of the Cargo Walls.



Secure Cargo



Mobile Seat



Dump Cart

To order an additional cart or any of our accessories, please use this Special Coupon Code "Cart" to get 15% OFF your total order. Please use the Coupon Code at Check Out on our website at: WWW.MIGHTYMAXCART.COM



USE AND CARE

- > Please call 888-730-2278 for missing parts or instructions.
- > Only expand flatbed in use for extra-large cooler or box

- > Wash off with fresh cart water after use in salt water or at the beach > When extended under a load, it is normal for cart to flex in the middle > Store your Tub and Cart empty indoors when not is use > Not intended for use in deep soft powdery sand.

All-Terrain Wheels are Imported Standard Wheel Colors are Black, Yellow, and Blue





Step 18. Set Tub Atop Cargo Walls



Step 19. Bungee Cords

The Heavy Duty Bunge Cords* can be used to secure your cooler or other cargo. * Color Matched Bungees for all Carts



Double Stack



Optional Fishing Pole Holders

Stack up to 3 tubs

SAVE 15% OFF YOUR NEXT ORDER

AVOID PLACING HEAVY ITEMS IN CENTER WHEN FULLY EXPANDED

Please Register Here for your Warranty: www.mightymaxcart.com



For All Returns

If you want to return your cart, please go to our website at www.MightyMaxCart.com and then scroll over the FAQ icon, scroll down and click on "Return Policy", then follow the instructions.

Models: PO600B Cooler Caddie PO600D Fishing Cart PO600C All Purpose Garden Cart PO600SP Special Cart (All accessories)



Step 20. Optional Hitch Assembly

Comes with 1-1/2" Black Nylon Bolt and Locking Wing Nut to fasten to the lower handle of the next-in-train towed cart.







Optional Garden Seat Coming Soon!

PARTS LIST: MODEL: PO600A			
	Part Description:	Quantity:	Part Number
	1) Front Frame 2) Rear Frame	1 1	FF-103 RF-104
	 Upper Handle Lower Handle 	1	UH-100 LH-101
	5) 5th Wheel 6) Wheel Assembly	1 4	FW-102 WA-108
	7) Axles8) Set of 2 Bungees in bag	2	SA-118
	Parts in Hardware Bag:		
	8) Friction Ring 9) 4.5" Hex Bolt 10) Black Spacer 11) Black Hex Nut 12) End Caps	1 1 2 2 4	FR-111 HB-115 SR-116 HN-114 EC-119
	 13) 2" Black Nylon Bolt 14) T-Wrench Tool 15) Assembly Instructions 16) Spring Clips 	1 1 5 1 2	FWD-117 TT-120 AS-126 VS-121
	Optional Accessories: (Models PO600B/PO6000		
	Cargo Walls Removable Tub Black Removable Tub Green Tool Rack	2 1 1	R-105 T-107 T-107G TR-106
	All Optional Accessorie	S:	
	Hitch Assembly Fishing Pole Holders Additional Tubs	1 2 1	H-110 FPH-124 T-107