






We asked contractors how we could improve on existing concrete screws, and the result of the feedback is the Titen Turbo screw anchor for concrete and masonry. Titen Turbo delivers what pros want — consistently trouble-free installation, and fastening strength they can depend on.

Typical concrete

screw anchor



Titen Turbo Flat-Head Screw US Patent 11,002,305

Titen Turbo Hex-Head Screw US Patent 11,002,305

Titen Turbo Trim-Head Screw US Patent 11,002,305

Concrete dust collects at bottom of hole

Torque Reduction Channel
Displaces Dust for Trouble-Free Installation

The secret behind the performance of the Titen Turbo screw anchor lies in its patented thread design, which enables smooth driving with less torque while providing superior holding power. The revolutionary Torque Reduction Channel between the threads gives drilling dust a place to go, thereby significantly reducing torque-related issues like binding, stripping and snapping without compromising strength.



Features

- Patented Torque Reduction Channel that displaces dust where it can't obstruct the thread action, reducing the likelihood of binding in the hole.
- Available with either a hex head or, for a flush profile, a 6-lobe-drive countersunk flat head or trim head.
- 6-lobe drive provides positive bit engagement resulting in easy installations and long bit life.
- 6-lobe bit included in packaging for countersunk flat-head and trim-head version.
- Superior tension load performance.
- Matched-tolerance bit not required; use a standard ANSI drill bit for installation.
- Serrated screw point for fast starts when fastening wood.
- Designed for installation with an impact driver or cordless drill. Installation using the Titen Turbo Installation Tool is recommended.
- Use in dry interior environments only.
- Code listed in accordance with ICC-ES AC193 for uncracked concrete and ICC-ES AC106 for masonry applications without cleaning dust from predrilled holes.

Codes:

IAPMO UES ER-712 (uncracked concrete) (City of LA Supplement within ER-712);

IAPMO UES ER-716 (masonry)
(City of LA Supplement within ER-716);

FL16230 (concrete and masonry)

Material: Carbon steel

Coating: Zinc plating with baked-on ceramic coating

Versatile Applications



Sliding door track installation




Window frames



Furring strips

Anatomy of the Titen Turbo (TNT) Concrete and Masonry Screw Anchor

Next Generation TNT screw anchor designed to improve installation experience with lower torque and higher loads than the competition.



For the first time, we are introducing a 6-lobe drive concrete and masonry screw anchor to provide improved installation experience. This design is superior to the standard Phillip's bit as it grabs better and allows for more torque to be provided for installation.

The revolutionary Torque Reduction Channel features a patented asymmetrical thread design with dust channel that allows more space for dust.

Serration on leading threads to effectively cut the concrete or masonry.

Pointed tip for easy attachment of wood to concrete or for wood-to-wood applications.

Blue Titen Turbo Product Data (3/16" diameter)

Size	Head Style Model No.		Drill Bit Dia.	Quantity	
5126			שווו פונ טומ.	Pack	Carton
3/16 X 1 1/4		TNT18114H		100	1,600
3/16 X 1 3/4		TNT18134H		100	500
3/16 X 21/4	1/4" Hex	TNT18214H	5/32"	100	500
3/16 X 23/4	74 nex	TNT18234H		100	500
3/16 X 31/4		TNT18314H		100	400
3/16 X 33/4		TNT18334H		100	400
3/16 X 1 1/4		TNT18114TF		100	1,600
3/16 X 13/4		TNT18134TF		100	500
3/16 X 21/4	T25 6-Lobe Flat	TNT18214TF	5/32"	100	500
3/16 X 23/4	120 0-Lone Flat	TNT18234TF	732	100	500
3/16 X 31/4		TNT18314TF		100	400
3/16 X 33/4		TNT18334TF		100	400

Blue Titen Turbo Product Data (1/4" diameter)

Cino	Hood Ctulo	Head Style Model No.		Qua	ntity
Size	Head Style			Pack	Carton
1/4 x 1 1/4		TNT25114H		100	1,600
1/4 x 13/4		TNT25134H		100	500
1/4 x 21/4		TNT25214H		100	500
1/4 x 23/4		TNT25234H		100	500
1/4 x 31/4	5/16" Hex	TNT25314H	3/ ₁₆ "	100	400
1/4 x 33/4		TNT25334H		100	400
1/4 x 4		TNT25400H		100	400
1/4 x 5		TNT25500H		100	400
1/4 x 6		TNT25600H		100	400
1/4 x 1 1/4		TNT25114TF		100	1,600
1/4 x 13/4		TNT25134TF		100	500
1/4 x 21/4		TNT25214TF		100	500
1/4 x 23/4	T30 6-Lobe Flat	TNT25234TF	3/16"	100	500
1/4 x 3 1/4		TNT25314TF		100	400
1/4 x 33/4		TNT25334TF		100	400
1/4 x 4		TNT25400TF		100	400

Black Titen Turbo Product Data (3/16" diameter)



	Size	Head Style	Model No.	Drill Bit Dia.	Quantity	
•	Size	neau Style	WIDUEI NO.	טוווו טונ טומ.	Pack	Carton
	3/16 X 1 1/4		TNTBL18114H		100	1,600
	3/16 X 1 3/4	1/4" Hex	TNTBL18134H	5/32"	100	500
	3/16 X 23/4	74 Hex	TNTBL18234H		100	500
	3/16 X 31/4		TNTBL18314H		100	400
	3/16 X 1 1/4		TNTBL18114TF		100	1600
	3/16 X 1 3/4		TNTBL18134TF		100	500
	3/16 X 21/4	T25 6-Lobe Flat	TNTBL18214TF	5/32"	100	500
	3/16 X 23/4		TNTBL18234TF		100	500
	3/16 X 31/4		TNTBL18314TF		100	400

Solution Black Titen Turbo Product Data (1/4" diameter)

Size	Hood Style	Head Style Model No.		Qua	ntity
3126	neau Style	Model No.	Drill Bit Dia.	Pack	Carton
1/4 x 1 1/4		TNTBL25114H		100	1,600
1/4 x 1 3/4		TNTBL25134H		100	500
1/4 x 21/4		TNTBL25214H	3/16"	100	500
1/4 x 23/4	1/4" Hex	TNTBL25234H		100	500
1/4 x 31/4		TNTBL25314H		100	400
1/4 x 33/4		TNTBL25334H		100	400
1/4 x 4		TNTBL25400H		100	400
1/4 x 1 3/4		TNTBL25134TF		100	500
1/4 x 21/4		TNTBL25214TF		100	500
1/4 x 23/4	T30 6-Lobe Flat	TNTBL25234TF	3/16"	100	500
1/4 x 3 1/4		TNTBL25314TF		100	400
1/4 x 4		TNTBL25400TF		100	400







White Titen Turbo Product Data (3/16" diameter)

Size	Head Style Model No.		Drill Bit Dia.	Quantity	
3126	neau Style	MOUEL NO.	Di ili bit Dia.	Pack	Carton
3/16 X 1 1/4		TNTW18114TF		100	1,600
3/16 X 1 3/4		TNTW18134TF	5/ ₃₂ "	100	500
3/16 X 21/4	T25 6-Lobe Flat	TNTW18214TF		100	500
3/16 X 23/4	120 0-Lone Flat	TNTW18234TF		100	500
3/16 X 31/4		TNTW18314TF		100	400
3/16 X 33/4		TNTW18334TF		100	400

White Titen Turbo Product Data (1/4" diameter)

Size	Head Style	Head Style Model No.		Quantity	
3126	neau Style	Model No.	Drill Bit Dia.	Pack	Carton
1/4 x 1 1/4		TNTW25114TF		100	1,600
1/4 x 1 3/4		TNTW25134TF		100	500
1/4 x 21/4	T30 6-Lobe Flat	TNTW25214TF	3/16"	100	500
1/4 x 23/4	130 6-Lobe Flat	TNTW25234TF	916	100	500
1/4 x 3 1/4		TNTW25314TF		100	400
1/4 x 33/4		TNTW25334TF		100	400
1/4 x 23/4		TNTW25234TTR	3/16"	100	500
1/4 x 23/4	T25 6-Lobe Trim	TNTW25234TTRB		1,000	_
1/4 x 3 1/4	120 6-LODE IIIII	TNTW25314TTR		100	400
1/4 x 3 1/4		TNTW25314TTRB		1,000	_

Silver Titen Turbo Product Data (6-Lobe Flat Head)

Size	Head Style	Model No.	Drill Bit Dia.	Quantity Box
3/16 X 13/4		TNTS18134TFB		1,000
3/16 X 23/4	T25 6-Lobe Flat	TNTS18234TFB	5/32"	1,000
3/16 X 33/4		TNTS18334TFB		1,000
1/4 x 23/4	T30 6-Lobe Flat	TNTS25234TFB	3/16"	1,000
1/4 x 3 1/4	130 O-LODE FIAL	TNTS25314TFB	716	1,000

Bronze Titen Turbo Product Data (6-Lobe Trim Head)

Size	Head Style Model No.		Bit Size	Quantity	
Size	Head Style	wouel No.	DIL SIZE	Box	Carton
1/4 x 23/4		TNTB25234TTR	3/16"	100	500
1/4 x 23/4	TOE & Lobo Trim	TNTB25234TTRB		1,000	_
1/4 x 3 1/4	T25 6-Lobe Trim	TNTB25314TTR		100	400
1/4 x 3 1/4		TNTB25314TTRB		1,000	_

Titen Turbo Installation Information and Additional Data¹

Characteristic	Symbol	Units	Nominal Ancho	Nominal Anchor Diameter (in.)				
Glidracteristic	Syllibol	UIIIIS	3/16	1/4				
Installation Information								
Drill Bit Diameter	d	in.	5/32	3/16				
Minimum Baseplate Clearance Hole Diameter	d_c	in.	1/4	5/16				
Minimum Hole Depth	h _{hole}	in.	21/4	21/4				
Embedment Depth	h _{nom}	in.	13⁄4	13/4				
Effective Embedment Depth	h _{ef}	in.	1.25	1.20				
Critical Edge Distance	C _{ac}	in.	3	3				
Minimum Edge Distance	C _{min}	in.	13⁄4	13/4				
Minimum Spacing	\mathcal{S}_{min}	in.	1	2				
Minimum Concrete Thickness	h _{min}	in.	31/4	31/4				
	Additional Data							
Yield Strength	f _{ya}	psi	100,000					
Tensile Strength	f _{uta}	psi	125,000					
Minimum Tensile and Shear Stress Area	A_{se}	in.²	0.0131	0.0211				

The information presented in this table is to be used in conjunction with the design criteria of ACI 318-19 Chapter 17, ACI 318-14 Chapter 17 or ACI 318-11 Appendix D.



Titen Turbo Tension Strength Design Data¹

Characteristic	Symbol	Units	Nominal Anchor	Diameter (in.)			
Glidiacteristic	Syllibul	UIIIIS	3/16	1/4			
Anchor Category	1, 2 or 3	_	1				
Embedment Depth	h _{nom}	in.	13⁄4	13/4			
	Steel Strength	in Tension					
Tension Resistance of Steel	N_{sa}	lb.	1,640	2,640			
Strength Reduction Factor — Steel Failure ²	$oldsymbol{arphi}_{sa}$	_	0.6	5			
	Concrete Breakout Str	ength in Tension					
Effective Embedment Depth	h _{ef}	in.	1.25	1.20			
Critical Edge Distance	C_{ac}	in.	3	3			
Effectiveness Factor — Uncracked Concrete	k _{uncr}	_	24	1			
Modification Factor	$\Psi_{c,N}$	_	1.0)			
Strength Reduction Factor — Concrete Breakout Failure ³	ϕ_{cb}		0.6	5			
Pullout Strength in Tension							
Pullout Resistance Uncracked Concrete (f'c = 2,500 psi) ⁵	$N_{p,uncr}$	lb.	1,515	1,515			
Strength Reduction Factor — Pullout Failure ⁴	$\phi_{\scriptscriptstyle ho}$	_	0.65				

- 1. The information presented in this table is to be used in conjunction with the design criteria of ACI 318-19 Chapter 17, ACI 318-14 Chapter 17 or ACI 318-11 Appendix D.
- 2. The tabulated value of ϕ_{Sa} applies when the load combinations of Section 1605.1 of the 2021 IBC, Section 1605.2 of the 2018, 2015, 2012, and 2009 IBC, ACI 318-19, ACI 318-14 Section 5.3 or ACI 318-11 Section 9.2 are used. If the load combinations of ACI 318-11 Appendix C are used, the appropriate value of ϕ must be determined in accordance with ACI 318-11 Section D.4.4.
- 3. The tabulated value of ϕ_{cb} applies when both the load combinations of Section 1605.1 of the 2021 IBC, Section 1605.2 of the 2018, 2015, 2012, and 2009 IBC, ACI 318-19, ACI 318-14 Section 5.3 or ACI 318-11 Section 9.2 are used and the requirements of ACI 318-19 Section 17.5.3, ACI 318-14 Section 17.3.3 (c) or ACI 318-11 Section D.4.3, as applicable, for Condition B are met. If the load combinations of ACI 318-11 Appendix C are used, the appropriate value of ϕ must be determined in accordance with ACI 318-11 Section D.4.4 for Condition B.
- 4. The tabulated value of ϕ_D applies when both the load combinations of Section 1605.1 of the 2021 IBC, Section 1605.2 of the 2018, 2015, 2012, and 2009 IBC, ACI 318-19, ACI 318-14 Section 5.3 or ACI 318-11 Section 9.2 are used and the requirements of ACI 318-19 Section 17.5.3, ACI 318-14 Section 17.3.3 (c) or ACI 318-11 Section D.4.3 (c) for Condition B are met. If the load combinations of ACI 318-11 Appendix C are used, the appropriate value of ϕ must be determined in accordance with ACI 318-11 Section D.4.4 for Condition B.
- 5. The characteristic pullout resistance for greater compressive strengths may be increased by multiplying the tabular value by (f'c/2500)^{0.23} for 1/4" screw anchors. No increase in the characteristic pullout resistance for greater compressive strengths is permitted for 3/16" screw anchors.

Titen Turbo Shear Strength Design Data Into Concrete¹

Characteristic	Symbol	Units	Nominal Anchor Diameter (in.)				
Glaracteristic	Syllibol	Units	3⁄16	1/4			
Anchor Category	1, 2 or 3	_	1				
Embedment Depth	h _{nom}	in.	13/4	13⁄4			
	Steel Strength in Shear						
Shear Resistance of Steel	V _{sa}	lb.	475	720			
Strength Reduction Factor — Steel Failure	ϕ_{sa}	_	0.60^{2}				
	Concrete Breakout St	rength in Shear					
Outside Diameter	d_a	in.	0.129	0.164			
Load Bearing Length of Anchor in Shear	I _e	in.	1.25	1.20			
Strength Reduction Factor — Concrete Breakout Failure	ϕ_{cb}	_	0.7	.03			
Concrete Pryout Strength in Shear							
Coefficient for Pryout Strength	k_{cp}	_	1.0				
Strength Reduction Factor — Concrete Pryout Failure	ϕ_{cp}	_	0.7	'O ³			

- The information presented in this table is to be used in conjunction with the design criteria of ACI 318-19 Chapter 17, ACI 318-14 Chapter 17 or ACI 318-11 Appendix D.
- 2. The tabulated value of ϕ_{Sa} applies when the load combinations of Section 1605.1 of the 2021 IBC®, Section 1605.2 of the 2018, 2015, 2012, and 2009 IBC, ACI 318-19 and ACI 318-14 Section 5.3, or ACI 318-11 Section 9.2 are used. If the load combinations of ACI 318-11 Appendix C are used, the appropriate value of ϕ must be determined in accordance with ACI 318-11 Section D.4.4.
- 3. The tabulated values of φ_{CD} and φ_{CD} apply when both the load combinations of Section 1605.1 of the 2021 IBC, Section 1605.2 of the 2018, 2015, 2012 and 2009 IBC, ACI 318-19, ACI 318-14 Section 5.3 or ACI 318-11 Section 9.2 are used and the requirements of ACI 318-19 Section 17.5.3, ACI 318-14 Section 17.3.3 (c) or ACI 318-11 Section D.4.3, as applicable, for Condition B are met. If the load combinations of ACI 318-11 Appendix C are used. the appropriate value of φ must be determined in accordance with ACI 318-11 Section D.4.4 for Condition B.



Allowable Tension Load for Titen Turbo Screw Anchor Installed in Face of Grouted CMU^{1,2,3}

Anchor	Embedment		Minimum Dimensions			
Diameter (in.)	Depth (in.)	Spacing (in.)	Edge (in.)	End (in.)	Allowable Load (lb.) ⁴	
3/16	2	3	37/8	37/8	267	
3/16	2	3	1½	37/8	267	
1/4	2	4	37/8	37/8	393	
1/4	2	4	1½	37/8	343	

- The tabulates values are for screw anchors installed in minimum 8"-wide grouted concrete masonry walls having reached a minimum f'm of 1,500 psi at time of installation.
- Embedment is measured from the masonry surface to the embedded end of the screw anchor.
- 3. Screw anchors must be installed in grouted cell. The minimum edge and end distances must be maintained.
- 4. Allowable loads are based on a safety factor of 5.0 for installations under the IBC® and IRC®.

Allowable Shear Load for Titen Turbo Screw Anchor Installed in Face of Grouted CMU^{1,2,3}

Anchor	Embedment	Minimum Dimensions				Allowable Load	
Diameter (in.)	Depth (in.)	Spacing (in.)	Edge (in.)	End (in.)	Direction of Loading	(lb.)4	
3/16	2	3	37/8	37/8	Toward edge, parallel to wall end	218	
3/16	2	3	11/2	37/8	Toward wall end, parallel to wall edge	218	
1/4	2	4	37/8	37/8	Toward edge, parallel to wall end	342	
1/4	2	4	11/2	37/8	Toward wall end, parallel to wall edge	283	

- The tabulates values are for screw anchors installed in minimum 8"-wide grouted concrete masonry walls having reached a minimum f'm of 1,500 psi at time of installation.
- 2. Embedment is measured from the masonry surface to the embedded end of the screw anchor.
- 3. Screw anchors must be installed in grouted cell. The minimum edge and end distances must be maintained.
- 4. Allowable loads are based on a safety factor of 5.0 for installations under the IBC and IRC.

Allowable Tension Load for Titen Turbo Screw Anchor Installed in Hollow CMU Wall Faces^{1,2,3}

Anchor	Embedment		Allowable			
Diameter (in.)	Diameter Depth (in.) (in.)		Edge (in.)	End (in.)	Load (lb.) ⁴	
3/16	1 1/4	3	31/8	37/8	117	
1/4	1 1/4	4	31/8	31/8	117	

- The tabulates values are for screw anchors installed in minimum 8"-wide hollow masonry walls having reached a minimum f'm of 1,500 psi at time of installation.
- 2. Embedment is the thickness of the face shell.

- Screw anchors may be installed at any location in the wall face provided the minimum edge and end distances are maintained.
- 4. Allowable loads are based on a safety factor of 5.0 for installations under the IBC and IRC.

Allowable Shear Load for Titen Turbo Screw Anchor Installed in Hollow CMU Wall Faces^{1,2,3}

Anchor	Embedment	Mi	nimum Dimensio	ons	Direction of	Allowable Load (lb.) ⁴	
Diameter (in.)	Depth (in.)	Spacing (in.)	Edge (in.)	End (in.)	Loading		
3/16	11⁄4	3	3%	37/8	Toward edge, parallel to wall end	164	
1/4	11⁄4	4	37/8	37/8	Toward edge, parallel to wall end	190	

- The tabulates values are for screw anchors installed in minimum 8"wide hollow masonry walls having reached a minimum f'm of 1,500 psi at time of installation.
- 2. Embedment is the thickness of the face shell.

- 3. Screw anchors may be installed at any location in the wall face provided the minimum edge and end distances are maintained.
- Allowable loads are based on a safety factor of 5.0 for installations under the IBC and IRC.



Titen Turbo Screw Anchor Installation Tool

Six-piece kit includes:

- 6-lobe bit socket
- T25 and T30 bits
- 1/4" and 5/16" hex sockets
- Canvas storage bag

Titen Turbo Installation Tool

Model	Quantity			
No.	Clamshell	Carton		
TNTINSTALLKIT	1	4		




Titen Turbo Screw Anchor Installation Kit

Installation Sequence







Titen® Screw Anchor — Drill Bits

Size	Model	Use	With	Quantity	
(in.)	No.	Screw	Length	Box	Carton
5/32 X 3 1/2	MDB15312C1		To 13/4	1	
5/ 41/	MDB15412C1	3/16" diameter	To 31/4	1	10
5⁄32 X 4 1∕2	MDB15412C4			4	
5/32 X 5 1/2	MDB15512C1		To 4	1	
3/16 X 3 1/2	MDB18312C1		To 13/4	1	
3/16 X 4 1/2	MDB18412C1	1/4"	To 3 1/4	1	10
	MDB18412C4	diameter		4	
3/16 X 5 1/2	MDB18512C1		To 4	1	

SDS-Plus® Drill Bits

Size (in.)	Model No.	For Screw Diameter (in.)	Drilling Depth (in.)	Overall Length (in.)
5⁄32 X 6	MDPL01506H	3/16	31/8	6
5/32 X 7	MDPL01507H	716	41/8	7
3∕16 X 5	MDPL01805H		2%	5
3∕16 X 6	MDPL01806H	1/4	31/8	6
3/16 X 7	MDPL01807H		41/8	7


Titen drivers are sold individually.

SDS-plus® is a trademark of the Robert Bosch Tool Corporation.

For use in attaching electrical boxes, conduits, switch boxes, light fixtures, window frames and more into concrete or masonry-based materials.



Thresholds















To locate your local dealer, visit strongtie.com/dealerlocator.